

# YPC40A36

by Burndy  
Catalog ID: YPC40A36

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:600 (61) - 800 (61)



## Product Details

### General

Die Index	T
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810138700
UPC 12 Digit	7818101387000

### Dimensions

Dimension - Height inch	3.70 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Dimension - Width inch	1.88 in

### Conductor Related

Conductor - ACSR Str Run Range	556.5 kcmil-795 kcmil
Conductor - ACSR Str Tap Range	336.4 kcmil-556.5 kcmil
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Run Range	600 kcmil-800 kcmil
Conductor - AL Str Tap	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Tap Range	397 kcmil-600 kcmil
Conductor - Copper Str Run	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Run Range	600 kcmil-800 kcmil
Conductor - Copper Str Tap	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - Copper Str Tap Range	397 kcmil-600 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• CU C Solid-Run</li> <li>• ACSR C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> <li>• CU C Solid-Tap</li> <li>• ACSR C Str-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)