

YTW36RD36REKHT

by Burndy
Catalog ID: YTW36RD36REKHT

Double Pad Non EHV Full Tension Deadend ACSS, Hardware TMH9, HAWK 477 (26/7) kcmil, YTW36RD36REKHTNT Aluminum Dead End Assy., BYNA36R15HHT Terminal



Product Details

General

Application	For ACSS Conductor, Corona free operation up to 230 KV
Connector Type	Deadend
Feature - Barrel Style	Tapered
Material	Aluminum
Physical Attribute - Number of Holes	8
Prefilled Oxide Inhibitor	N
UPC	781810516744
UPC 12 Digit	7818105167444

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	HAWK 477 (26/7) kcmil
Conductor - ACSS Str Size Range	477 (26/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)