

# BRISTOL SERIES

BRISTOL PARK (LED)

## FEATURES

- LED heat sink and an LED engine containing 12 high powered indirect LEDs
- Upper housing is a die cast aluminum dome top secured to a one-piece die cast aluminum top assembly
- Optics are narrow beams designed to provide glare free indirect lighting



## SPECIFICATIONS

### CONSTRUCTION

- All cast aluminum parts shall be low copper alloy A356. All extruded aluminum parts shall be alloy 6061-T6, 6063-T5 or equal. The Lower Housing is .125" wall 6063-T5 extruded aluminum which connects to the top the mounting tenon with internal bolts, inaccessible after installation
- All fasteners shall be Corrosion Resistant. When tamper resistant fasteners are required, spanner HD (snake eye) style shall be provided (special tool required, available at additional cost)
- Beacon LED Bollards feature a removable and upgradeable LED module and heat sink. The drivers shall be mounted on a removable plate. The heat sink shall be 356 cast aluminum. Each LED is provided with one optical, 12 degree wide beam Type V lenses. The Heat Sink & LED Array shall be mounted to a mounting plate and pointed upwards into an indirect reflector
- Finish shall be a Beacote V polyester powder-coat electro-statically applied and thermocured. Beacote V finish shall consist of a five stage iron phosphate chemical pretreatment regimen with a polymer primer sealer, oven dry off, and top coated with a thermoset super TGIC polyester powder coat finish. The finish shall meet the AAMA 605.2 performance specification which includes passing a 3000 hour salt spray test for corrosion resistance and resists cracking or loss of adhesion per ASTM D522 and resists surface impacts of up to 160 inch-pound

### ELECTRICAL

- Luminaire shall have a minimum CRI of 67 at 5000K
- Shall be able to operate normally in ambient temperatures from -40°C to 40°C
- Luminaires are equipped with LED driver(s) that accept 90 through 305 VAC, 50 Hz to 60 Hz (UNIV). Power factor is .92 at full load. All driver components supplied are component-to-component wiring within the luminaire will carry no more than 80% of rated current and is listed by UL for use at 600VAC at 50°C or higher. Plug disconnects are listed by UL for use at 600 VAC, 15A or higher
- The on-board surge protector shall be a UL recognized component for the United States and Canada and have a surge current rating of 20,000 Amps using the industry standard 8/20 pSec wave. The LSP shall have a clamping voltage of 825V and surge rating of 540J. The case shall be a high-temperature, flame resistant plastic enclosure

### MOUNTING

- A high strength steel mounting plate, hot-dip galvanized after fabrication, is secured and double-nut leveled to the concrete footing with 5/8" x 24" x 3" hot dipped galvanized anchor bolts, hex head nuts and washers on a 4 3/4" – 6" bolt circle

### CERTIFICATIONS

- The luminaire shall bear an NRTL label and be marked suitable for wet locations

### WARRANTY

- 5 year warranty
- See [HLI Standard Warranty](#) for additional information

# BRISTOL SERIES

BRISTOL PARK (LED)

## ORDERING GUIDE


**Example:** BRP42-AC-24NB-55-3K-UNV-IND5-AB-CES-BLT

CATALOG # \_\_\_\_\_

Series	Lens Finish	Engine Watts	CCT-Color Temp	Voltage	Optics
<b>BRP42</b> Bristol Park	<b>AC</b> Acrylic, clear	<b>24NB-55</b> 55 Watts - LED array	<b>3K</b> 3000K <b>4K</b> 4000K <b>5K</b> 5000K	<b>UNV</b> 120-277V	<b>IND5</b> Indirect Type V 360° (std.)

Mounting Options	Style Options	Control Options
<b>AB</b> Anchor Base	<b>CES</b> Chain Eye, single <b>CED</b> Chain Eye, double	<b>BLT</b> Black Matte Textured <b>BLS</b> Black Gloss Smooth <b>DBT</b> Dark Bronze Matte Textured <b>DBS</b> Dark Bronze Gloss Smooth <b>GTT</b> Graphite Matte Textured <b>LGS</b> Light Grey Gloss Smooth <b>PSS</b> Platinum Silver Smooth <b>WHT</b> White Matte Textured <b>WHS</b> White Gloss Smooth <b>VGT</b> Verde Green Textured
		Color Option
		<b>CC</b> Custom Color

## DIMENSIONS



## USE OF TRADEMARKS AND TRADE NAMES

All product and company names, logos and product identifies are trademarks™ or registered trademarks® of Hubbell Lighting, Inc. or their respective owners. Use of them does not necessarily imply any affiliation with or endorsement by such respective owners.