


## BDBLCS10LV2DW

by Burndy  
Catalog ID: BDBLCS10LV2DW



BURNDY® VERSIPOLE™ Aluminum Lay-in Distribution blocks. 600 Volt Rated; Listed to UL1953. Allows for continuous Run Conductors. Acceptable for Panel mounting or DIN Rail mounting for medium and large sizes. Rated for use with code and flex conductor without requiring ferrules. AL9CU dual rated for use with copper and aluminum conductors. Supplied with Black Cover.

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing

## Product Details

### General

Item Type	M
Material - Base	NYLON 6/6
Material - Mounting Hardware	Stainless steel
Material Type - Screw	Tin plated Aluminum
Number Of Poles	2
UPC	621945553491
UPC 12 Digit	621945553491

### Dimensions

Height	4.10 in
Length	12 in

### Electrical Ratings

Amperage Rating	475
Voltage Rating	600 V

### Conductor Related

Conductor - Copper DLO Size Range	Run - 777 Kcmil, Tap - 535 Kcmil
Conductor - Copper Flex H Run Range	500-750 Flex
Conductor - Copper Flex H Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Flex I Run Range	500-750 Flex
Conductor - Copper Flex I Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Flex K Run Range	500-750 Flex
Conductor - Copper Flex K Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Str Run	500-750 Kcmil
Conductor - Copper Str Tap	# 4 Awg - 500 Kcmil

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)