


BDBLCS13LR3DW

by Burndy
Catalog ID: BDBLCS13LR3DW



BURNDY® VERSIPOLE™ Aluminum Lay-in Distribution blocks. 600 Volt Rated; Listed to UL1953. Allows for continuous Run Conductors. Acceptable for Panel mounting or DIN Rail mounting for medium and large sizes. Rated for use with code and flex conductor without requiring ferrules. AL9CU dual rated for use with copper and aluminum conductors. Supplied with Black Cover.

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing

Product Details

General

| | |
|------------------------------|---------------------|
| Item Type | M |
| Material - Base | NYLON 6/6 |
| Material - Mounting Hardware | Stainless steel |
| Material Type - Screw | Tin plated Aluminum |
| Number Of Poles | 3 |
| UPC | 621945553705 |
| UPC 12 Digit | 621945553705 |

Dimensions

| | |
|--------|----------|
| Height | 4.10 in |
| Length | 17.84 in |

Electrical Ratings

| | |
|-----------------|-------|
| Amperage Rating | 545 |
| Voltage Rating | 600 V |

Conductor Related

| | |
|-------------------------------------|--|
| Conductor - Copper DLO Size Range | Run - 1111 Kcmil, Tap - # 6 Awg - 4/0 Str. |
| Conductor - Copper Flex H Run Range | 750 - 1000 Flex |
| Conductor - Copper Flex H Tap Range | # 6 Awg - 4/0 Str. Flex |
| Conductor - Copper Flex I Run Range | 750 - 1000 Flex |
| Conductor - Copper Flex I Tap Range | # 6 Awg - 4/0 Str. Flex |
| Conductor - Copper Flex K Run Range | 750 - 1000 Flex |
| Conductor - Copper Flex K Tap Range | # 6 Awg - 4/0 Str. Flex |
| Conductor - Copper Str Run | 750 - 1000 Kcmil |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)