


## BDBLCS13LV1DW

by Burndy  
Catalog ID: BDBLCS13LV1DW

BURNDY® VERSIPOLE™ Aluminum Lay-in Distribution blocks. 600 Volt Rated; Listed to UL1953. Allows for continuous Run Conductors. Acceptable for Panel mounting or DIN Rail mounting for medium and large sizes. Rated for use with code and flex conductor without requiring ferrules. AL9CU dual rated for use with copper and aluminum conductors. Supplied with Black Cover.

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing



## Product Details

### General

Item Type	M
Material - Base	NYLON 6/6
Material - Mounting Hardware	Stainless steel
Material Type - Screw	Tin plated Aluminum
Number Of Poles	1
UPC	621945549753
UPC 12 Digit	621945549753

### Dimensions

Height	4.10 in
Length	6.16 in

### Electrical Ratings

Amperage Rating	545
Voltage Rating	600 V

### Conductor Related

Conductor - Copper DLO Size Range	Run - 1111 Kcmil, Tap - # 4 Awg - 500 Kcmil
Conductor - Copper Flex H Run Range	750 - 1000 Flex
Conductor - Copper Flex H Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Flex I Run Range	750 - 1000 Flex
Conductor - Copper Flex I Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Flex K Run Range	750 - 1000 Flex
Conductor - Copper Flex K Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Str Run	750 - 1000 Kcmil

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)