



* Representative image

TRANSFORMER BRACKET, 3-POSITION, ALUMINUM BANDED STYLE with NEMA A and B LUG SPACING for 7-3/4in to 12-1/4in DIA. POLES

by CHANCE Utility
Catalog ID: C15M3969

Aluminum, banded style transformer bracket for mounting 3 transformers with NEMA A or B lug spacing. Includes six 5/8" x 2-1/2" square head machine bolts and nuts for type A or B transformer lugs.

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,500 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 1,950 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,600 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,350 lbs. maximum recommended per phase for 3 simultaneous loads
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

Product Details

General

Material	6061-T6 Aluminum
Type	Banded Pole Mount Bracket
UPC	096359294306

Dimensions

Distance From Pole	<ul style="list-style-type: none"> • 9 in • 6 in
Weight	49 lb

Logistics

Pallet Quantity	6 EA
-----------------	------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com