



YAG28L2NTCFXTZ

by Burndy

Catalog ID: YAG28L2NTCFXTZ

Uninsulated Copper Compression Terminal, Tin-Zinc Plated, UL Listed 90° C, Up to 35 kV, 2 Hole

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- 45° and 90° angular lugs are available
- please contact Customer Service
- Tin-Zinc plated for battery connectors or other heavy duty equipment, reduce the corrosion from lead/acid batteries
- Connectors are clearly marked with stamping and barrel color coding
- Connectors accommodate both Flex and Code Wire

Product Details

General

Application	• The use of Tin-Zinc is becoming more prevalent • we are seeing this used in appliances, aerospace, automotive, electrical connectors, marine equipment, mining, and other industries
Construction Material - Main	Copper tubing tin - zinc plated
Die Index	15
Material	Copper
Number of Holes	2
Sub Brand	HYLUG
Type	Cable to Flat
UPC	621945555846

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1-1/16 in
Dimension - Stud Size inch	1/2 in
Length	4.65 in
Thickness	0.15 in

Conductor Related

Conductor - Copper DLO Size	4/0 (550/24) DLO
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)