



# Strain Carrier, 8' Dist.

by CHANCE Utility  
Catalog ID: C4010410



\* Representative image

STRAIN CARRIER, 8' DIST. This tool assembly has the same basic use as the two-pole strain carrier: Relieving strain while removing a single string of insulators. The distribution strain carrier has a compression deadend yoke at the hot end which is equipped with a various shoe sizes to grip the conductor ahead of insulator-conductor hardware with a compression lever type action, gripping tighter as the load increases. The various shoes furnished with the kit fit conductors from 0.292" through 0.806" (No. 2 through 397.5 ACSR). Maximum load rating for each distribution strain-carrier assembly listed below is 6,500 lb. per insulator string.

## Product Details

### General

Style	Two Pole Strain Carrier - Distribution
UPC	096359017554

### Dimensions

Length	96 in
Weight	82 lb

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)