



**Oh No!**  
IMAGE COMING SOON

## Insulated Hydraulically Operated Conductor Cutter For Up To 954 MCM ACSR, 6'

by CHANCE Utility  
Catalog ID: C4030731

HYDRAULIC WIRE CUTTER - 6FT - 954 ACSR, This tool is used to cut conductors up to 954 MCM ACSR, All-Aluminum and 500 MCM copper. Operation is similar to that of a hydraulic jack- a knob-handle is turned to enable the lineman to operate the pump handle. When the cut is completed, the knob is turned in the opposite direction to allow the cutting head to open. The Epoxiglas pole, handle and hydraulic hose have been tested to 100 kV per foot. Hydraulic oil has a dielectric strength of 25 + kV per ASTM D877-64. The hose has a minimum burst strength of 12,000 PSI. The pump provides a maximum pressure of 9,000 PSI. Features include jaws designed to cut without flattening the conductor. The jaws are also adjustable to compensate for wear. The hydraulic hose is located outside the pole for easy maintenance. It is extremely well balanced, requiring minimum effort to cut large conductors.

### Product Details

#### General

|                       |   |
|-----------------------|---|
| Storage Bag Included? | T306-0007 (Bag not included. Must be ordered separately.) |
| Style                 | Scissors Jaw  |
| Type                  | Cutters   |
| UPC                   | 096359018469  |

#### Dimensions

|        |          |
|--------|----------|
| Length | 72 in    |
| Weight | 18.13 lb |

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)