



# Carrier, Strain

by CHANCE Utility  
Catalog ID: C4012177

HD DUTY TWO-POLE STRAIN CARRIER, NPL 7', Two-pole Strain Carriers relieve strain from an insulator string to permit removal from energized lines. Normally used on a single string of insulators, these carriers sometimes are used for multiple strings where conductor-end hardware permits attachment. Yokes are fabricated from high-strength aluminum plate and include a steel chain assembly for anchoring the back plate to the structure. Conductor-end yoke includes a hook and three machined sockets (C401-1860, -1892, -1894). Two-pole Strain Carriers relieve strain from an insulator string to permit removal from energized lines. Normally used on a single string of insulators, these carriers sometimes are used for multiple strings where conductor-end hardware permits attachment.



\* Representative image

## Product Details

### General

Style	Two Pole Strain Carrier - Transmission
UPC	096359017790

### Dimensions

Length	120 in
Maximum Distance Between Yokes	129
Minimum Distance Between Yokes	95
Weight	89 lb

### Electrical Ratings

Voltage - Maximum	302000 V
-------------------	----------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)