



# Terminal, Aluminum Compression

by ANDERSON  
Catalog ID: CCLS1424D

Terminal, Aluminum Compression, Cable to Flat, Short Barrel, cable range 1.345-1.424 pad: 4 hole, 4 in. TERMINAL, AL COMP 1.345-1.424 IN, D PAD

- 90° pad orientation available, 45° pad orientation available, 15° pad orientation available



\* Representative image

## Product Details

### General

Material	Aluminum
Number of Bolt Holes	4
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Terminal, Cable to Flat
UPC	096359297772

### Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	1.960 lb
Width - Pad	4 in

### Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

### Conductor Related

Conductor Compatibility	ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61
Conductor Diameter - Maximum	1.424 in

Conductor Diameter - Minimum	1.345 in
Conductor Diameter Range	1.345 - 1.424
Conductor Type	<ul style="list-style-type: none"><li>• AAC</li><li>• ACSR</li></ul>

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsh@hubbell.com](mailto:hpscsh@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)