



Terminal, Aluminum Compression

by ANDERSON
Catalog ID: CCLS1300D

Terminal, Aluminum Compression, Cable to Flat, Short Barrel, cable range 1.246-1.3 pad: 4 hole, 4 in. TERMINAL, AL COMP 1.246-1.300 IN, D PAD

- 90° pad orientation available, 45° pad orientation available, 15° pad orientation available



* Representative image

Product Details

General

Material	Aluminum
Number of Bolt Holes	4
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Terminal, Cable to Flat
UPC	096359297734

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	1.568 lb
Width - Pad	4 in

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61
Conductor Diameter - Maximum	1.3 in
Conductor Diameter - Minimum	1.246 in

Conductor Diameter Range	1.246 - 1.3
Conductor Type	• AAC • ACSR

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com