

# CE250N008

by Acme Electric

Catalog ID: CE250N008



ICT .250KVA 240X480-120

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Feedback

## Product Details

### General

<p>Application</p>	<p>Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.</p>
--------------------	---

Color	Black
Secondary Voltage	120 V
UPC	047503015292

## Dimensions

Dimensions	4.547 in x 4.5 in x 5.2897 in
Height	5.2897 in
Length	4.547 in
Weight	10 lb
Width	4.5 in

Feedback

## Electrical Ratings

Primary Voltage	240 X 480 V
-----------------	-------------

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• cUL Listed</li></ul>
------------------	--

## Logistics

Carton Quantity	1
Pallet Quantity	72