

CE50N008

by Acme Electric
 Catalog ID: CE50N008



ICT .050KVA 240X480-120

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Feedback

Product Details

General

<p>Application</p>	<p>Acme’s TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer’s windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme’s TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.</p>
--------------------	---

Color	Black
Secondary Voltage	120 V
UPC	047503015247

Dimensions

Dimensions	3.32 in x 3 in x 4.0397 in
Height	4.0397 in
Length	3.32 in
Weight	2.6 lb
Width	3 in

Feedback

Electrical Ratings

Primary Voltage	240 X 480 V
-----------------	-------------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• cUL Listed
------------------	--

Logistics

Carton Quantity	1
Pallet Quantity	168