



# BOLT, CLEVIS, 5/8in x 10in

By Chance  
Catalog # 15810



Commonly used for attaching suspension insulators or other deadend applications.

## Features

- 4" thread length and cone pointed end
- Includes one square nut
- Clevis opening is 13/16" wide with 1/2" dia. x 2-1/2" long hex cotter bolt, hex nut and cotter key
- Rated tensile strength is 12,400 lbs.
- Galvanized per ASTM A-153
- RUS listed, ef - Bolt,clevis

## General

Catalog Number	15810
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	12400 lb.
UPC	096359068884

## Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	10 in
Length - Threaded Area	4 in
Weight	1.95 lb

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
RUS Listed Reference	ef - Bolt, clevis

## Logistics

Pallet Quantity	1200
-----------------	------

## Product Assets

- [Catalogs - Communications Catalog](#)
- [Sales Drawings - Clevis Bolt 5/8](#)
- [Specifications - 15810](#)



A Hubbell brand