



0° Communication Standoff Bracket, 15"

By Chance
Catalog # 1CSM150

15" Medium Duty Fiberglass 0° Communication Standoff Bracket



*Representative Image

General

| | |
|--|---------------------|
| Catalog Number | 1CSM150 |
| Description - End Fitting | Communication clamp |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 800 lb |
| Strength Rating - Minimum Ultimate, Transverse (T) | 1,500 lb |
| Strength Rating - Minimum Ultimate, Vertical (V) | 1,800 lb |
| UPC | 096359722052 |

Dimensions

| | |
|---------------------------|-------------------|
| Diameter - Rod / Tube | 1.5 in |
| Distance From Pole | 15 in |
| Length | 15 in |
| Mounting Bolt Spacing | 6.00 in - 8.00 in |
| Radius - FWDE Wrap-Around | 1.5 |
| Weight | 4.2 lb |

Electrical Ratings

| | |
|-------|---------|
| Phase | 1-Phase |
|-------|---------|

Logistics

| | |
|------------------|-----|
| Carton Quantity | 9 |
| Pallet Quantity | 216 |
| Standard Package | 1 |

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - Communications Catalog](#)
- [Sales Drawings - SA-1CSM120](#)
- [Video - Hubbell | CHANCE® Communication Stand Off Bracket](#)



A Hubbell brand