



## Horizontal Pin Standoff Bracket, 15"

By CHANCE Utility  
Catalog # [1SBM15H2](#)

15" Medium Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1" Nylon Threads



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	Horizontal Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1450 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1500 lb

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	15 in
Length	15.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	5.6 lb

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-25\)](#)



A proud member of the Hubbell Family.