



Vertical Pin Standoff Bracket, 36" Two-Phase

By Chance

Catalog # [2SBH36VV2](#)

36" Heavy Duty Fiberglass Two-Phase Vertical Pin Standoff Bracket with 1" Nylon Threads



*Representative Image

General

Catalog Number	2SBH36VV2
Description - End Fitting	Vertical Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	2000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2550 lb
UPC	096359624301

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	36 in
Length	36 in
Mounting Bolt Spacing	5 in
	6 in
	8 in
Weight	20.8 lb

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)

[Sales Drawings - 2 Phase, Heavy Duty Vertical Insulator Pin, Nylon](#)

[Nylon](#)