



Vertical Pin Standoff Bracket, 36" Two-Phase

By Chance
Catalog # 2SBH36VV2



*Representative Image

Features

- Vertical Position Pin Type Insulator Bracket
- 2" (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

General

Catalog Number	2SBH36VV2
Description - End Fitting	Vertical Pin
Material - Threads	Nylon
Strength Rating - Minimum Ultimate, Longitudinal (L)	2000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2550 lb
UPC	096359624301

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	36 in
Length	36 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5 in• 6 in• 8 in
Weight	20.8 lb

Electrical Ratings

Phase	2-Phase
-------	---------

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - 2 Phase, Heavy Duty Vertical Insulator Pin, Nylon](#)
[Specifications - 2SBH36VV2](#)