



Anchor, Lead/Adapter, SS5, 8/10/12 X 5.5ft Twineye

By Chance

Catalog # [126542AEJ](#)

Square Shaft (SS 5) Lead Section, 5' (1524 mm) long with 8" (203 mm) - 10" (254 mm) - 12" (304 mm) Helices with Guy Adapter Twineye in separate box.



Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

General

Application	Helical Anchoring
Catalog Number	126542AEJ
Coating	Galvanized, ASTM A-153
Eyenuit Style	Twineye
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. Note: Pulling Eye Rated: 12,000 lbs. Guy wire should not be attached to pulling eye.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Type	Lead Sections
UPC	096359068495

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in
Length	60 in
Weight	90.65 lb

Logistics

Standard Package 1

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - SS5 Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance Literature - Anchoring](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - SA126542AE](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-126542AEJ-SPEC-EN | REV 6/2024