



CROSSARM INSULATOR PIN with 1-3/8in NYLON THREAD, CLAMP TYPE STYLE

By Chance
Catalog # 143221P



Insulator pin used to support pin type insulator with 1-3/8" NEMA internal thread on crossarm.

Features

- Includes two 5 /8" x 7" carriage bolts, two square nuts, two curved lock nuts and a 5 /16" x 1-1 /2" washer plate
- Cantilever load rating is 1,500 lbs. based on ANSI/IEEE 10 degree deflection criterea
- Hot dip galvanized per ASTM A-153
- RUS Listed, f - Pin, crossarm

General

Catalog Number	143221P
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Pins
UPC	096359404149

Dimensions

Dimensions	14.000 in x 6.000 in x 5.000 in
Distance From Pole	N/A

Height	5 in
Length	14 in
Length - Threaded Area	3
Weight	6.1 lb
Width	6 in

Certifications And Compliance

RUS Listed Reference	f - Pin, crossarm
----------------------	-------------------

Logistics

Carton Quantity	8
Pallet Quantity	192

Product Assets

- [Catalogs - Pole Line Hardware Supplements](#)
- [Installation Manuals - CHANCE® Nylon Thread Insulator Pin Instructions](#)
- [Sales Drawings - Straight Corner Pin](#)
- [Specifications - 143221P](#)