



# MF TYPE CURVED LOCK NUT, 5/8in THREAD

By Chance  
Catalog # [3512](#)



Used with regular square nuts to create a vibration resistant fit. When the MF lock nut contacts the regular nut, turn an additional 1/2 to 3/4's turn with wrench to firmly lock in place.

### Features

- For 5/8" diameter bolt, tapped 5/8-11-UNC
- Hot dip galvanized per ASTM A-153
- RUS listed, ek - Locknut.

### General

Catalog Number	3512
Coating	Galvanized, ASTM A-153
Material	Steel
UPC	096359070221

### Dimensions

Dimensions	0.938 in x 0.938 in x 0.250 in
Distance From Pole	N/A
Height	0.25 in
Length	0.938 in
Weight	0.04 lb
Width	0.938 in

### Certifications And Compliance

RUS Listed Reference	ek - Locknut
----------------------	--------------

### Logistics

Pallet Quantity	45000
-----------------	-------

### Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Pole Line Hardware](#)
- [Sales Drawings - MF Lockout](#)