



15° Communication Standoff Bracket, 12"

By CHANCE Utility
Catalog # 1CSM12

12" Medium Duty Fiberglass 15° Communication Standoff Bracket



*Representative Image

General

Description - End Fitting	Communication clamp
Strength Rating - Minimum Ultimate, Longitudinal (L)	1300 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2100 lb
UPC	096359239321

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	12 in
Length	12.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	3.8 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	216
Standard Package	1

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-33\)](#)
[Catalogs - Communications Catalog \(CA12042E\)](#)
[Sales Drawings - Standoff, Communications \(SA1CSM12\)](#)
[Video - Hubbell | CHANCE® Communication Stand Off Bracket \(CENT_CN_VI_EN_00085\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-1CSM12-SPEC-EN | REV 7/2023