



## MF TYPE CURVED LOCK NUT, 5/8in THREAD

By CHANCE Utility  
Catalog # [3512](#)

Used with regular square nuts to create a vibration resistant fit. When the MF lock nut contacts the regular nut, turn an additional 1/2 to 3/4's turn with wrench to firmly lock in place.



\*Representative Image

### Features

- For 5/8" diameter bolt, tapped 5/8-11-UNC
- Hot dip galvanized per ASTM A-153
- RUS listed, ek - Locknut.

### General

Coating	Galvanized, ASTM A-153
Material	Steel
UPC	096359070221

### Dimensions

Distance From Pole	N/A
Weight	0.04 lb

### Certifications and Compliance

RUS Listed Reference	ek - Locknut
----------------------	--------------

### Logistics

Pallet Quantity	45000
-----------------	-------

### Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)  
[Catalogs - Pole Line Hardware](#)  
[Sales Drawings - MF Lockout \(SA3510\)](#)

### Related Products

[6813 - WASHER, SQ FLAT, 5/8in SIZE, 2 1/4in](#)  
[6805 - WASHER, ROUND, 11/16in HOLE, 1 3/4in DIA.](#)  
[PSHB580175 - BOLT, MACHINE, HEX HEAD, 5/8in x 1-3/4in](#)  
[8812 - BOLT, MACHINE, SQ HEAD, 5/8in x 12in](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-3512-SPEC-EN | REV 4/2023