



MF TYPE CURVED LOCK NUT, 3/4in THREAD

By CHANCE Utility
Catalog # [3513](#)

Used with regular square nuts to create a vibration resistant fit. When the MF lock nut contacts the regular nut, turn an additional 1/2 to 3/4's turn with wrench to firmly lock in place.



*Representative Image

Features

- For 3/4" diameter bolt, tapped 3/4-10-UNC
- Hot dip galvanized per ASTM A-153
- RUS listed, ek - Locknut.

General

Coating	Galvanized, ASTM A-153
Material	Steel
UPC	096359070238

Dimensions

Distance From Pole	N/A
Weight	0.05 lb

Certifications and Compliance

RUS Listed Reference	ek - Locknut
----------------------	--------------

Logistics

Pallet Quantity	27000
-----------------	-------

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Pole Line Hardware](#)
[Sales Drawings - MF Lockout \(SA3510\)](#)

Related Products

[8914 - BOLT, MACHINE, SQ HEAD, 3/4in x 14in](#)
[6818 - WASHER, SQ FLAT, 13/16in HOLE, 4in SQ](#)
[6806 - WASHER, ROUND, 13/16 in HOLE, 2in](#)
[8884 - DOUBLE-ARMING BOLT, 3/4in x 14in w/4 NUTS](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-3513-SPEC-EN | REV 7/2023