



0° 2-Position Cutout / Arrester
Standoff Bracket w/ Hardware &
Spacer Bars(No Collars), 48" 13" 3-
Phase

By Chance
Catalog # 3SBM4813SGLSB



*Representative Image

48" 13" Medium Duty Fiberglass 0° 2-Position Cutout / Arrester
3-Phase Standoff Bracket w/ Hardware & Spacer Bars (No
Collars)

Features

- Single position end fitting with spacer bar
- 1.5" (medium duty) fiberglass rod
- 0° angle
- Base is aluminum alloy, end fitting is hot dip galvanized ductile iron

General

Catalog Number	3SBM4813SGLSB
Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum	700 lb
Ultimate, Longitudinal (L)	
Strength Rating - Minimum	5000 lb
Ultimate, Transverse (T)	
Strength Rating - Minimum	900 lb
Ultimate, Vertical (V)	
UPC	096359495628

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	13 in
Length	48 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6 in• 8 in
Weight	13.5 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Pallet Quantity	5
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - 1 \(2\) Position \(0°\) Three-Phase](#)
[Specifications - 3SBM4813SGLSB](#)