



15° 1-Position Cutout / Arrester Standoff Bracket w/ Hardware, 15"

By CHANCE Utility
Catalog # [1SBM15AMB](#)



15" Medium Duty Fiberglass 15° 1-Position Single-Phase Cutout / Arrester Bracket w/ Hardware

Features

- Not recommended for use with TripSaver® Reclosers

General

Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1500 lb
UPC	096359408208

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	15 in
Length	15.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	6.6 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Carton Quantity	6
Pallet Quantity	144
Standard Package	6

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-42\)](#)
[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-1SBM15AMB-SPEC-EN | REV 7/2023