



# Vertical Pin Standoff Bracket, 48" Two-Phase w/ Nylon

By Chance  
Catalog # [2SBH48VV2](#)

48" Heavy Duty Fiberglass Two-Phase Vertical Pin Standoff Bracket with 1" Nylon Threads

### Features

- Vertical Position Pin Type Insulator Bracket
- 2" (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

### General

Catalog Number	2SBH48VV2
Description - End Fitting	Vertical Pin
Material - Threads	Nylon
Strength Rating - Minimum Ultimate, Longitudinal (L)	1500 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2250 lb
UPC	096359574156

### Dimensions

Diameter - Rod / Tube	2 in
Dimensions	48 in x 24.5 in x 2.75 in
Distance From Pole	48 in
Height	2.75 in
Length	48 in



\*Representative Image

Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 5 in</li><li>• 6 in</li><li>• 8 in</li></ul>
Weight	24.68 lb
Width	24.5 in

### Electrical Ratings

Phase	2-Phase
-------	---------

### Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

### Logistics

Pallet Quantity	24
Standard Package	1

### Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Sales Drawings - SA\\_2SBHXXVV2](#)
- [Sales Drawings - 2 Phase, Heavy Duty Vertical Insulator Pin, Nylon](#)
- [Specifications - 2SBH48VV2](#)



A Hubbell brand