



15° 2-Position Cutout / Arrester Standoff Bracket, 36" 13" Three-Phase (No Hardware)

By Chance
Catalog # 3SBM3613AMT



*Representative Image

36 13 Medium Duty 15° 2-Position Three-Phase Cutout / Arrester Standoff Bracket (No Hardware)

Features

- Two position ("T" bracket) end fitting
- 1.5" (medium duty) fiberglass rod
- 15° angle
- Base is hot dip galvanized ductile iron, end fitting is aluminum alloy

General

Catalog Number	3SBM3613AMT
Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359397946

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	13 in
Length	36 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6 in• 8 in
Weight	19.6 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Carton Quantity	5
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - Standoff With Cast "T" End Ferrule](#)
[Specifications - 3SBM3613AMT](#)