



Rod, Expanding/Cross-Plate Anchor, 3/4in X 8ft Twineye

By Chance
Catalog # 5358

Expanding/Cross-Plate Anchor Rod 0.75" (19.1 mm) Diameter
Rod, 8' (2438 mm) long with Twineye.

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading,kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Application

Earth Tension Anchoring

General

Catalog Number	5358
Coating	Galvanized, ASTM A-153
Eyenum Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb.
Type	Anchor Rod
UPC	096359072508

Dimensions

Dimensions	96.000 in x 2.000 in x 1.250 in
Height	1.25 in



Length	96 in
Rod Diameter	0.75 in
Weight	12.74 lb
Width	2 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
Certified Listed	<ul style="list-style-type: none">••
Industry Standard(s)	NEMA Standard
RUS Listed Reference	x – Rod, anchor

Logistics

Pallet Quantity	50
Standard Package	5

Product Assets

- Catalogs - Anchor Tools
- Catalogs - Anchors
- Catalogs - Dependable Anchoring Solutions
- Catalogs - Communications Catalog
- Installation Manuals - TD06135E_Expanding_Anchors
- Installation Manuals - TD06136E_Cross_Plate_Anchors
- Installation Manuals - Holding Capacity Chart - Soil Classification
- Sales Drawings - Threaded Twineye Rod - 3/4"
- Sales Drawings - 3/4 Threaded Twineye Rod
- SDS - MSDS - Galvanized Steel Products
- Specifications - 5358
- Video - CHANCE Expanding Anchors