



BOLT, SPOOL, DOUBLE-UPSET, 5/8in x 14in

By Chance
Catalog # 7834



Spool bolts are used to support a spool insulator in the horizontal position in secondary applications. Industry slang is Upset Bolt.

Features

- 6" thread length and cone pointed end
- Overall length is 19-3/4"
- Pole offset distance is 1"
- Includes one square nut with cotter key
- Rated cantilever load is 800 lbs.
- Hot dip galvanized per ASTM A-153
- Manufactured in compliance with ANSI C135.31
- RUS listed, q - Bolt, double upset

General

Catalog Number	7834
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Double Upset
UPC	096359242499

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	20.500 in x 1.750 in x 1.750 in
Distance From Pole	N/A
Height	1.75 in
Length	20.5 in
Length - Threaded Area	6 in
Weight	1.86 lb
Width	1.75 in

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

- [Catalogs - Pole Line Hardware](#)
- [Sales Drawings - Upset Spool Bolts Single And Double](#)
- [Specifications - 7834](#)



A Hubbell brand