



0° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware & Spacer Bars(No Collars), 48" 13" 3-Phase

By Chance

Catalog # [3SBM4813SGLSB](#)



*Representative Image

48" 13" Medium Duty Fiberglass 0° 2-Position Cutout / Arrester 3-Phase Standoff Bracket w/ Hardware & Spacer Bars (No Collars)

General

Catalog Number	3SBM4813SGLSB
Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	5000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359495628

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	13 in
Length	48 in
Mounting Bolt Spacing	6 in
	8 in
Weight	13.5 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Pallet Quantity	5
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - 1 \(2\) Position \(0°\) Three-Phase](#)



A Hubbell brand