



BOLT, MACHINE, SQ HEAD, 1/2in x 12in



By Chance
Catalog # 8712

Square head machine bolt for utility pole and crossarm construction. Rated for 7,800 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

Height	0.8 in
Length	12.75 in
Length - Threaded Area	6 in
Weight	0.67 lb
Width	0.8 in

General

Catalog Number	8712
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	7800 lb.
Type	Machine Bolts
UPC	096359075301

Certifications And Compliance

Industry Standard(s)	ANSI C135.1
RUS Listed Reference	c - Bolt, machine

Logistics

Pallet Quantity	3000
-----------------	------

Dimensions

Diameter	0.5 in
Diameter (Fraction)	1/2 in
Dimensions	12.750 in x 0.800 in x 0.800 in
Distance From Pole	N/A

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - Bolts, Machine 1/2"](#)
- [Specifications - 8712](#)



A Hubbell brand