



## TWO-BOLT STATIC WIRE BRACKET, with 1/2in DIA. LINK, 14in LENGTH

By Chance  
Catalog # 5433

Bracket used with suspension clamp (ordered sperately) to support static wires. Load plate is welded to the rods, while the back plate can be adjusted to fit the pole.

### Features

- Designed for 10" to 12" dia. poles
- Bolt diameter is 5/8"
- Furnished with two square and two MF lock nuts
- Plates are curved for installation on round poles
- Galvanized steel per ASTM A-153

### General

Catalog Number	5433
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Supports
UPC	096359072577

### Dimensions

Dimensions	18.000 in x 8.500 in x 2.500 in
Distance From Pole	N/A
Height	2.5 in
Length	18 in
Length - Threaded Area	6 in
Weight	6.37 lb
Width	8.5 in

### Certifications And Compliance

RUS Listed Reference	ed - Support, overhead ground wire
----------------------	------------------------------------

### Logistics

Pallet Quantity	160
-----------------	-----

### Product Assets

- [Catalogs - Brackets, Shield Wire Support \(5-53-33\)](#)
- [Sales Drawings - Brackets, Shield Wire Support](#)





A Hubbell brand