



BOLT, MACHINE, SQ HEAD, 5/8in x 16in

By CHANCE Utility
Catalog # 8816



Square head machine bolt for utility pole and crossarm construction. Rated for 12,400 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Machine Bolts
UPC	096359075547

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Length	16.00 in
Length - Threaded Area	6
Weight	1.37 lb

Certifications and Compliance

Industry Standard(s)	ANSI C135.1
RUS Listed Reference	c - Bolt, machine

Logistics

Pallet Quantity	1440
-----------------	------

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Machine Bolts & DA Bolts \(5-53Supp24-28\)](#)
[Sales Drawings - 5/8 Machine Or Crossarm Bolt \(SA8802\)](#)

Related Products

[C2050186 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 5/8in SIZE](#)
[6813 - WASHER, SQ FLAT, 5/8in SIZE, 2 1/4in](#)
[3512 - MF TYPE CURVED LOCK NUT, 5/8in THREAD](#)
[6805 - WASHER, ROUND, 11/16in HOLE, 1 3/4in DIA.](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-8816-SPEC-EN | REV 7/2023