



## BOLT, SPOOL, DOUBLE-UPSET, 5/8in x 12in

By CHANCE Utility  
Catalog # [7832](#)

Spool bolts are used to support a spool insulator in the horizontal position in secondary applications. Industry slang is Upset Bolt.



\*Representative Image

### Features

- 6" thread length and cone pointed end
- Overall length is 17-3/4"
- Pole offset distance is 1"
- Includes one square nut with cotter key
- Rated cantilever load is 800 lbs.
- Hot dip galvanized per ASTM A-153
- Manufactured in compliance with ANSI C135.31
- RUS listed, q - Bolt, double upset

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Spool Bolts
UPC	096359074519

### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	12.00 in
Length - Threaded Area	6
Weight	1.76 lb

### Logistics

Pallet Quantity	1250
-----------------	------

### Product Assets

[Catalogs - Pole Line Hardware](#)

[Sales Drawings - Upset Spool Bolts Single And Double \(SA7740\)](#)

### Related Products

[3512 - MF TYPE CURVED LOCK NUT, 5/8in THREAD](#)

[C2050186 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 5/8in SIZE](#)

[6813 - WASHER, SQ FLAT, 5/8in SIZE, 2 1/4in](#)

[6805 - WASHER, ROUND, 11/16in HOLE, 1 3/4in DIA.](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-7832-SPEC-EN | REV 4/2023