



BOLT, MACHINE, SQ HEAD, 5/8in x 20in



By Chance
Catalog # 8820

Square head machine bolt for utility pole and crossarm construction. Rated for 12,400 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

Distance From Pole	N/A
Height	1 in
Length	20.5 in
Length - Threaded Area	6 in
Weight	1.68 lb
Width	1 in

General

Catalog Number	8820
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Machine Bolts
UPC	096359075561

Certifications And Compliance

Industry Standard(s)	ANSI C135.1
RUS Listed Reference	c - Bolt, machine

Logistics

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 5/8 Machine Or Crossarm Bolt](#)
- [Specifications - 8820](#)

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	20.500 in x 1.000 in x 1.000 in



A Hubbell brand