



DOUBLE-ARMING BOLT, 3/4in x 12in w/4 NUTS



By Chance
Catalog # 8882

Full thread double-arming bolt for utility pole double arm construction. Rated for 18,350 lbs. tensile strength. Includes four assembled square nuts and cone point. Industry slang is DA bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Catalog Number	8882
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
UPC	096359075806

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Dimensions	12.625 in x 1.125 in x 1.125 in

Distance From Pole	N/A
Height	1.125 in
Length	12.625 in
Weight	1.83 lb
Width	1.125 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.1
----------------------	-------------

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - Double-Arming Bolt](#)
- [Specifications - 8882](#)



A Hubbell brand