




34.5kV, 200kV LIW, 600A, ALTD Switch with Loadbreak Arc Chutes.

By Chance

Catalog # [ALTD06200RLBC](#)

34.5kV, 200kV LIW, 600A, Line Tension Disconnect Switch with Loadbreak Arc Chutes.



Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 38kV 200kV BIL Voltage Class/Insulation Level
- 600A and 900A Non-Load Break Style Current Ratings
- 600A Load Break Style
- Extension Links and Terminal Connector Options

General

Blade Type	Solid Copper (two blade truss-member)
Catalog Number	ALTD06200RLBC
Color - Insulator	Dark Gray
Contact	Silver, Copper
Insulator Type	ESP™ Polymer
Tension Range	15000 lb

Dimensions

Weight	17.25 lb
--------	----------

Electrical Ratings

Arc Distance - Dry	15.3" (388.6mm)
BIL	200 kV
Creep and Leakage Distance	31.4" (797.6mm)
Current Overload - 8hr	1080 A
Emergency	
Current Rating	600 A
Dead-Ending Rating - Working Load	15,000 Lbs
Interrupt Rating - 600 A	25 Operations
Reference Voltage Limit - Minimum	34.5kV
Temperature Rise - Max. at 600A	28°C
Voltage - Maximum	38 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical
Withstand Current - Short Time (10 cycles)	40kA, assymetrical

Certifications And Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

Logistics

Pallet Quantity	12 EA
Standard Package	1

Product Assets

[Catalogs - Hookstick Operated Switches](#)
[Sales Drawings - Loadbreak ALTD Switch](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-ALTD06200RLBC-SPEC-EN | REV 6/2024