



# RH Opening, 38kV, 200kV BIL, 900A Recloser Bypass Switch with Pole Mount Bracket

By Chance  
Catalog # [BP3B9M](#)

Righthand Opening, 38kV, 200kV LIW, 900A Recloser Bypass Switch with Pole Mount Bracket.



\*Representative Image

## Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 and 38kV ratings
- 110, 125 and 150kV BIL ratings
- 600A and 900A ratings
- ESP Polymer 2.25" Bolt Circle Insulator Assemblies
- Right Hand and Left Hand opening Options
- Non-Angled and Angled Bypass Blade Options
- Cross arm or Pole Mount Options
- 3 Phase on 100" or 124" Cross Arms in Steel or Fiberglass

## General

Blade Type	Solid Copper (two blade truss-member)
Cantilever Bending Strength - Routine	800 Lbs (3.559kN)
Catalog Number	BP3B9M
Color - Insulator	Dark Gray
Contact	Silver
EU RoHS Indicator	No
Insulator Type	N/A
Material - Base	Galvanized Steel per ASTM A153
Tension Range	5000 lb
Torsional Strength	3,000 in Lbs (339 N-M)
UPC	096359827344

## Dimensions

Weight	181 lb
--------	--------

## Electrical Ratings

Arc Distance - Dry	15.7"(399mm)
BIL	200 kV
Creep and Leakage Distance	52"(1,320mm)
Current Overload - 8hr	1620 A
Emergency	
Reference Voltage Limit - Minimum	38kV
Temperature Rise - Max. at 600A	33° C
Voltage - Maximum	38 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical
Withstand Current - Short Time (10 cycles)	65kA peak

## Certifications And Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

## Logistics

Standard Package	1
------------------	---

## Product Assets

[Catalogs - Hookstick Operated Switches](#)  
[Literature - HPS/CHANCE® TYPE BP3 SWITCH](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-BP3B9M-SPEC-EN | REV 6/2024