




LH Opening, 25kV, 125kV BIL, 600A Bypass Switch with No Mounting Provisions

By Chance
Catalog # [BP3L2C](#)

Lefthand Opening, 25kV, 125kV LIW, 600A Bypass Switch with No Mounting Provisions.



Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 and 38kV ratings
- 110, 125 and 150kV BIL ratings
- 600A and 900A ratings
- ESP Polymer 2.25" Bolt Circle Insulator Assemblies
- Right Hand and Left Hand opening Options
- Non-Angled and Angled Bypass Blade Options
- Cross arm or Pole Mount Options
- 3 Phase on 100" or 124" Cross Arms in Steel or Fiberglass

General

Blade Type	Solid Copper (two blade truss-member)
Cantilever Bending Strength - Routine	1,000 Lbs (4.45kN)
Catalog Number	BP3L2C
Color - Insulator	Dark Gray
Contact	Silver
Insulator Type	N/A
Material - Base	Galvanized Steel per ASTM A153
Tension Range	5000 lb
Torsional Strength	3,000 in Lbs (339 N-M)
UPC	096359712398

Electrical Ratings

Arc Distance - Dry	8.1" (205.7mm)
BIL	125 kV
Creep and Leakage Distance	21.9" (556.3mm)
Current Overload - 8hr	1080 A
Emergency	
Reference Voltage Limit - Minimum	25kV
Temperature Rise - Max. at 600A	33° C
Voltage - Maximum	29 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical
Withstand Current - Short Time (10 cycles)	65kA peak

Certifications And Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Hookstick Operated Switches](#)
- [Literature - HPS/CHANCE® TYPE BP3 SWITCH](#)
- [Sales Drawings - By-Pass 3-Pull Switch](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-BP3L2C-SPEC-EN | REV 6/2024