



# BRACKET, TRANSFORMER, BANDED CLUSTER, ALUMINUM

By Chance  
Catalog # [C10M29](#)

Aluminum Banded Transformer Cluster, for mounting two 3 through 100 kVa transformers. For transformers of 167 through 250 kVa with four position NEMA C lugs order adapter plate C321-A. Refer to chart for loading information.

## Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,500 lbs. maximum recommended per position
- 18" = 1,950 lbs. maximum recommended per position
- 22" = 1,600 lbs. maximum recommended per position
- 26" = 1,350 lbs. maximum recommended per position
- For replacement bolts order four each P2160185P

## General

Catalog Number	C10M29
EU RoHS Indicator	No
Material	6061-T6 Aluminum
Type	Banded Pole Mount Bracket
UPC	096359353935



\*Representative Image

## Dimensions

Distance From Pole	9 in
Weight	14.7 lb

## Certifications And Compliance

Buy America(n) Qualified      Contact Manufacturer

## Product Assets

- [Catalogs - Aluminum Hardware & Apitong Wood](#)
- [Installation Manuals - Banded Aluminum Cluster Mount](#)
- [Installation Instructions](#)
- [Sales Drawings - Mount, Double Band Cluster](#)
- [Specifications - C10M29](#)
- [Video - CHANCE Banded Transformer Bracket](#)



A Hubbell brand