



RH Opening, 25kV, 150kV BIL, 900A 3 Phase Bypass Switch with Pole Mounting Bracket

By Chance
Catalog # [BP3R7PY](#)

Righthand Opening, 25kV, 150kV LIW, 900A Bypass Switch with Pole Mounting Bracket.

Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 and 3 kV ratings
- 110, 125 and 150kV BIL ratings
- 600A and 900A ratings
- ESP Polymer 2.25" Bolt Circle Insulator Assemblies
- Right Hand and Left Hand opening Options
- Non-Angled and Angled Bypass Blade Options
- Cross arm or Pole Mount Options
- 3 Phase on 100" or 124" Cross Arms in Steel or Fiberglass

General

Blade Type	Solid Copper (two blade truss-member)
Cantilever Bending Strength - Routine	800 Lbs (3.56kN)
Catalog Number	BP3R7PY
Color - Insulator	Dark Gray
Contact	Silver
Insulator Type	Polymer (2 1/4" Bolt Circle)
Material - Base	Galvanized Steel per ASTM A174
Tension Range	5000 lb
Torsional Strength	3,000 in Lbs (339 N-M)

Dimensions

Weight	460 lb
--------	--------

Electrical Ratings



*Representative Image

Arc Distance - Dry	10" (254mm)
BIL	150 kV
Creep and Leakage Distance	28.2" (716.3mm)
Current Overload - 8hr	1080 A
Emergency	
Phase	Three Phase
Reference Voltage Limit - Minimum	25kV
Temperature Rise - Max. at 600A	33° C
Voltage - Maximum	29 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical
Withstand Current - Short Time (10 cycles)	65kA peak

Certifications And Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Hookstick Operated Switches](#)
- [Installation Manuals - BP3 Instructions \(TD10321E Rev. B - 07/2021\)](#)
- [Literature - HPS/CHANCE® TYPE BP3 SWITCH](#)
- [Sales Drawings - 3-Phase, By-Pass, 3 Pull Switch](#)
- [Specifications - BP3R7PY](#)



A Hubbell brand