



Anchor, Lead/Adapter, SS150, 8/10 X 3ft Tripleye

By CHANCE Utility
Catalog # [C11013263AE](#)

Square Shaft (SS 150) Lead Section 3' (914 mm) long with 8" (203 mm) - 10" (254 mm) Helices with Guy Adapter Tripleye attached.



*Representative Image

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Eyenuit Style	Tripleye
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	7000 ft-lbs
Type	Lead Sections

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Length	36.000 in
Weight	49.70 lb

Logistics

Standard Package 1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Sales Drawings - SA11013262AE](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [C1100389 - Anchor, Extension, SS150, X 7ft](#)
- [C1100470 - Anchor, Extension, SS150, X 5ft](#)
- [C1100440 - Anchor, Extension, SS150, X 10ft](#)
- [C1100388 - Anchor, Extension, SS150, X 3.5ft](#)
- [PSC2030521 - Tripleye® ANCHOR ROD BONDING CLAMP for SS & RR ANCHOR ADAPTERS and NO-WRENCH ANCHOR EXTENSION](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C11013263AE-SPEC-EN | REV 1/2024