



# TRANSFORMER BRACKET, 3-POSITION, ALUMINUM RACK STYLE with LIFTING EYE and NEMA A and B LUG SPACING

By CHANCE Utility  
Catalog # C11MW24LB

Bracket, Transformer



\*Representative Image

## Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,500 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 2,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,640 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,385 lbs. maximum recommended per phase for 3 simultaneous loads
- Bracket can be field adjusted for NEMA A or B lug spacing
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

## General

Type Bolted Pole Mount Bracket  
UPC 096359589129

## Logistics

Pallet Quantity 5

## Product Assets

- [Installation Manuals - Proper Alignment of Bolt Head \(P216-0256\)](#)
- [Sales Drawings - Transformer Rack, Wing \(SA11MW24L\)](#)
- [Technical Solutions - CH-C11MW24LB-SPEC-EN](#)



A proud member of the Hubbell Family.