



ANCHOR, LEAD, SS150 10X12X14in

By Chance
Catalog # [C1100838](#)

Square Shaft (SS 150) Lead Section, 7' (2134 mm) long with 10" (254 mm) -12" (304 mm) -14" (355 mm) Helices.



Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

General

Application	Helical Anchoring
Catalog Number	C1100838
Coating	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	7000 ft-lbs
Type	Lead Sections
UPC	096359498704

Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in
Dimensions	84.000 in x 14.000 in x 14.000 in
Height	14 in
Length	84 in
Weight	96 lb
Width	14 in

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Installation Manuals - Holding Capacity Chart - SS150 Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance Literature - Anchoring](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - SA1100838](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C1100838-SPEC-EN | REV 6/2024