



TRANSFORMER BRACKET, 3-POSITION, ALUMINUM RACK STYLE with LIFTING EYE and NEMA A and B LUG SPACING

By CHANCE Utility
Catalog # [C11MW2412ABLG](#)

Bracket, Transformer



*Representative Image

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,500 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 2,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,640 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,385 lbs. maximum recommended per phase for 3 simultaneous loads
- Bracket can be field adjusted for NEMA A or B lug spacing
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

General

Type Bolted Pole Mount Bracket
UPC 096359583530

Logistics

Pallet Quantity 8

Product Assets

[Catalogs - Aluminum Hardware & Apitong Wood \(5B\)](#)
[Installation Manuals - Proper Alignment of Bolt Head \(P216-0256\)](#)
[Sales Drawings - Transformer Rack, Wing \(SA11MW2412ABLG\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C11MW2412ABLG-SPEC-EN | REV 4/2023