




TRANSFORMER BRACKET, 3-POSITION, ALUMINUM RACK STYLE with LIFTING EYE and NEMA A and B LUG SPACING

By Chance
Catalog # [C11MW24L](#)



Bracket, Transformer, Wing-Rack Type.

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,500 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 2,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,640 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,385 lbs. maximum recommended per phase for 3 simultaneous loads
- Bracket can be field adjusted for NEMA A or B lug spacing
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

General

Catalog Number	C11MW24L
Material	6061-T6 Aluminum
Type	Bolted Pole Mount Bracket
UPC	096359355151

Dimensions

Dimensions	26.000 in x 12.000 in x 27.000 in
Height	27 in
Length	26 in
Weight	49 lb
Width	12 in

Logistics

Pallet Quantity	5
-----------------	---

Product Assets

[Catalogs - Aluminum Hardware & Apitong Wood](#)
[Installation Manuals - Proper Alignment of Bolt Head](#)
[Sales Drawings - Transformer Rack, Wing](#)



A Hubbell brand