



**TRANSFORMER BRACKET, 3-
POSITION, ALUMINUM BANDED
STYLE w/NEMA A, B and C LUG
SPACING for 9-1/2in to 19-1/2in
DIA. POLES**

By Chance
Catalog # [C15M361436](#)

Aluminum, banded style transformer bracket for mounting 3 transformers with NEMA A, B or C lug spacing. Includes six 5/8" x 2-1/2" square head machine bolts and nuts for type A, B or C transformer lugs.

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 5,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 3,900 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 3,200 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 2,700 lbs. maximum recommended per phase for 3 simultaneous loads
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

General

Catalog Number	C15M361436
EU RoHS Indicator	No
Material	6061-T6 Aluminum
Type	Banded Pole Mount Bracket

UPC 096359365440

Dimensions

Distance From Pole	6
Weight	71.569 lb

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Logistics

Pallet Quantity 2

Product Assets

[Catalogs - Aluminum Hardware & Apitong Wood](#)
[Installation Manuals - Banded Aluminum Cluster Mount](#)
[Installation Instructions](#)
[Sales Drawings - Mount, Jumbo Cluster](#)
[Sales Drawings - SA15M391436](#)
[Specifications - C15M361436](#)
[Video - CHANCE Banded Transformer Bracket](#)



A Hubbell brand